

bright Chair 2

Brochure



Dentium

bright Chair 2



Clear Visual Field


Up to 50,000 LUX, ensuring clarity and a wide view with a broad FOV



Blue Light Filtering Function

Maximized Spatial Efficiency

Compact size allows use of remaining space when installing chair





bright chair 2
Shortcut to
Promotional Video



Worthy Long Lasting Tech

Robust floor mount type structure allows for long-term use without minor breakdowns




One Person Treatment

Specially designed self-section module for easy single user treatment




Chair Dimension


Chair Out Size




Chair Up




Chair Down





Chair Out Size



Backrest Up



Backrest Down



Specification

Lift System	Hydraulic
Lift Height	490mm ~ 750mm (250mm)
Recline Range	0° ~ 65° (65°)
Headrest	Two-Joint
Dental Light	LED Light
Controller	Switch + LCD
Spittoon	Manual Rotation

Seat Color



Most Selected



Instrument

Line up (Basic)

High Handpiece	Low Handpiece	Coupling
 <p>M800L(NSK) Optic</p> <ul style="list-style-type: none"> · Power : 23W · Speed : 380,000~450,000min⁻¹ · Head Size : ø 10.6 x H12.4 mm 	   <p>FX205 M4/FX65/FX25(NSK) Non-Optic</p> <ul style="list-style-type: none"> · Midwest 4 hole · Max : 25,000 min⁻¹ 	 <p>PTL-CL-LED(NSK) Optic</p> <ul style="list-style-type: none"> · For NSK · Stainless Body · Titanium Coating · LED Coupling  <p>KCL-LED(KAVO) Optic</p> <ul style="list-style-type: none"> · For KaVo® MULTIflex® LUX with water volume adjuster · Stainless Body · Titanium Coating · LED Coupling
 <p>M900L(NSK) Optic</p> <ul style="list-style-type: none"> · Power : 26W · Speed : 325,000~430,000min⁻¹ · Head Size : ø 10.8 x H12.1 mm  <p>M800KL(NSK) Optic</p> <ul style="list-style-type: none"> · Power : 23W · Speed : 380,000~450,000min⁻¹ · Head Size : ø 10.6 x H12.4 mm  <p>M900KL(NSK) Optic</p> <ul style="list-style-type: none"> · Power : 26W · Speed : 325,000~430,000min⁻¹ · Head Size : ø 12.1 x H13.3 mm 	<h3 data-bbox="743 898 823 931">Scaler</h3>  <p>bright Scaler(Dentium)</p> <ul style="list-style-type: none"> · 28kHz~32kHz · 71g  <p>Varios 170(NSK)</p>  <p>dmetec</p>	

Option

High Handpiece	Angle	Motor
 <p>Z900L(NSK) Optic</p> <ul style="list-style-type: none"> · Power : 23 W, Speed : 360,000 ~ 440,000 min⁻¹ · Head Size : ø 12.5 x H13.1mm  <p>Z800L(NSK) Optic</p> <ul style="list-style-type: none"> · Power : 23 W, Speed : 360,000 ~ 440,000 min⁻¹ · Head Size : ø 10.8 x H12.1mm 	  <p>M65/M25(NSK) Non-Optic</p> <p>M25L(NSK) Optic</p> <ul style="list-style-type: none"> · Stainless Body · Backflow Prevention Valve · Midwest 4 hole · Max : 25,000 min⁻¹  <p>M95L(NSK) Optic</p> <ul style="list-style-type: none"> · 4-point Douche Spray · For FG.Bur(ø1.6) · Ceramic Ball Bearing · Max Speed : 200,000mi 	 <p>bright Elec(Dentium)</p> <ul style="list-style-type: none"> · Speed : 40,000rpm±10% · Torque : 3.0Ncm±10% · Weight : 62g · Light : Led light, 10,000lux  <p>M205(NSK)</p> <ul style="list-style-type: none"> · Stainless Body · Backflow Prevention Valve · Midwest 4 hole · Max : 25,000 min⁻¹  <p>NLX nano(NSK)</p> <ul style="list-style-type: none"> · Speed : 1,000 – 40,000 min⁻¹ (NLXBF) · Torque : Max. 3.4Ncm · Weight : 61g (micromotor only) · Light : White LED

Dentium

Dentium



This publication is for international distribution. It may differ from the certification and sales products in some countries.

BRC2_2023.08 [Rev.0]

76, Changyong-daero 256beon-gil, Yeongtong-gu, Suwon-si, Gyeonggi-do, Korea 16229

E-mail : overseas@dentium.com / www.globaldentium.com